

PRO218A DYNAMIC BASS DRUM MICROPHONE

Description

PRO218A is designed for bass drum, its tailored response, specific magnetic structure and vibration protection system are quite different with others, it features wide linear dynamic range by high SPL capacity. PRO218A is the best choice for bass drum or other bass instruments.

Features

- Tailored low frequency response.
- Tender and stout in bass.
- Low disturbance when impedance varies, high gain before feedback, high dynamic range.
- Low noise, high SPL capacity.
- Suitable to use for bass drum or other wide dynamic range instrument miking.

Included



Pouch



YA2 Threaded Adapter




HM27S MIC Clip



Specifications

Type	Dynamic
Polar Pattern	Supercardioid
Frequency Response	20 – 10,000 Hz
Sensitivity	-64 dBV/Pa (0.6 mV)
Output Impedance	45 Ω
Min. Load Impedance	150 Ω
Max. SPL	174 dB
Finish	Titanium blue
Connector	XLR3M
Dimensions	Ø58 × 140 mm (Ø2.28" × 5.51")
Net Weight	350 g (12.3 oz.)

PRO218A Frequency Response (Supercardioid)



PRO218A
EN

This information sheet contains important information for the safe use of the product. Read and follow the safety and handling instructions given here. Please keep this information sheet for future reference. If you pass on the product described overleaf, please enclose this information sheet.

Safety instructions

Intended use

This device converts acoustic signals in electrical signals. Any other use or use under the conditions excluded here is considered improper and can lead to personal injury or property damage. Neither the manufacturer nor the distributor is liable for damage resulting from improper use.

Choking hazard for children



Make sure that plastic sleeves, packaging, etc. cannot get into the reach of babies and small children. Do not allow children to use electrical devices unsupervised. They could loosen parts of the product, then swallow them and choke on them!

Place of operation

The device must not be used

- ▶ at particularly high temperatures or humidity
- ▶ in particularly dusty or polluted places
- ▶ in places where it can be exposed to moisture

General handling

To prevent damage, never use force when handling the product. Never immerse the product in liquids. Just wipe it with a clean, dry cloth. Never use liquid cleaners such as benzene, thinner, or flammable detergents to clean the product.

Disposal

Old devices



Devices with this label are subject to the current EU directive on waste electrical and electronic equipment (WEEE directive) and may not be disposed of with household waste, but only via a suitable disposal company. Ask your local authority or your specialist dealer about your options for proper disposal.

Packagings



Environmentally friendly materials have been selected for the packaging and are to be recycled. Do not just throw away plastic sleeves, packaging, etc., but recycle them. If necessary, note the instructions and labels on the packaging.